LA 300 Piston Pumps





A rotating manifold allows independent orientation of the filter and air motor sections for installation adaptability. Additionally, filter blocks may be positioned near guns or regulators to minimize pressure drops. Use with LA 380 pressure regulators eliminates the need for return drainpipes, further increasing placement options. Wall-mount, lid-mount and system-trolley configurations are available to meet specific installation requirements.

A 7:1 air-to-fluid ratio delivers precise application when paired with LA 380 pressure regulators. High flow rates allow use of lower pressure, reducing risk of adhesive shearing. Higher flow capability also reduces the need to use multiple pumps in high flow applications. LA 300 pumps accommodate 20-, 30- and 200-liter (5- or 55-gallon) containers. The versatile systems offer both standard and wear-resistant rods to handle a wide range of adhesives and production needs.

LA 300 pumps use no Teflon[®] seals or parts and the lubricating oil is U.S. Food and Drug Administration approved, making the pumps acceptable for use in food and tobacco industries.

® Teflon is a registered trademark of E.I. DuPont de Nemours and Company.

Specifications

<u>LA 300 Piston Pumps</u> Maximum Pump Rate	120 l/hr (31.7 gal/hr)	9
Maximum Adhesive Pressure	42 bar (600 psi)	1
Ambient Temperature	1 to 50° C (33 to 122° F)	
Suction Lift (Wet) @ 3000 mPas	4 m (13 ft)	
Air-to-fluid Pressure Ratio	7:1	
Maximum Air Consumption	1.8 NI/s (3.8 scfm)	
Minimum Recommended Air Line I.D.	8 mm (5/16 in.)	
Sound Intensity	<70 db	
Weight	15.5 kg (34 lbs)	
LA 380 Pressure Regulators Control Air Pressure Ambient Temperature	0 to 6 bar (0 to 85 psi) 1 to 50° C (33 to 122° F)	
Output Pressure Range Weight	LA 381 0 to 7 bar (0 to 100 psi) 4.5 kg (10 lbs)	LA 382 0 to 18 bar (0 to 5 kg (11 lbs)





to 250 psi)

LA 383 0 to 48 bar (0 to 700 psi)

5 kg (11 lbs)



For more information, talk with your Nordson representative or contact your Nordson regional office.

United States Canada Europe Japan Asia/Australia/ Duluth, Georgia Markham, Ontario Udenhout, The Netherlands Tokyo, Japan Latin America Telephone: (81) 3-5762-2700 Telephone: (800) 683-2314 Telephone: (800) 463-3200 Telephone: (31) 13-511-8777 Amherst, Ohio Facsimile: (905) 475-8821 Facsimile: (31) 13-511-3995 Facsimile: (81) 3-5762-2701 **Toll-free Facsimile:** Telephone: (440) 985-4797 (866) 667-3329 Facsimile: (440) 985-1096 www.nordson.com



When you expect more.®